

FM-2: Filter Monitor with Volumizer

The new Filter Monitor is an innovative system to alert when a filter needs to be changed via color-coded lights at the base of the faucet. The battery-powered FM-2 has five timers for a 5-stage system, as well as a water volumizer and programmable set-points and alarms for each function, all in a crisp, attractive housing.

FEATURES

- A five-stage filter monitor with five independent timers and a tri-color LED faucet indicator disc.
- Counts time and volume for up to five stages (can be less).
- The LED indicator disc will illuminate a green, yellow or red light when the water is turned on. The color indicates the percentage of elapsed time and volume used.
- Auto-Off function conserves battery power. The unit shuts off automatically after 5 minutes of non-use.
- The timer counts down in months or days (settings can be modified).
- The volumizer counts up in gallons or liters (settings can be modified).
- Includes an audible alarm (beep).
- Modern design is perfect for any kitchen.
- Installs easily.



 **1 YEAR WARRANTY**

SPECIFICATIONS

Timer Range: 0-999 days/months

Timer Modes: Days or months (default is months)

Volume Range: 0-99999 Gallons / Liters

Volume Modes: Gallons (default) or Liters

Volume Accuracy: +/-1% (at typical pressure; low and high pressures may affect accuracy)

Settings: One alert per stage, up to five stages

Default Setting: 12 months

Batteries: 2 x AA (included)

Battery Life: approx. 18 months

Base Unit Dimensions: 100 x 63 x 23 mm (4 x 2.5 x 0.9 in)

Base Unit Weight: 119 g (4.2 oz.) (including batteries)

Flow Sensor Cable Length: 93 cm (36.6 in)

Flow Sensor Fitting Size: 1/4" Quick Connect

LED Faucet Indicator Disc: Works with any non-air gap filter faucet

LED Faucet Indicator Disc Cable Length: 92 cm (36.25 in)

LED Faucet Indicator Disc Dimensions: 4.75 (1 1/4" in.) dia., 8 cm (5/16") high

PATENTS PENDING

Distributed By:

**APPLIED
MEMBRANES INC.®**

2325 Cousteau Ct., Vista, CA 92081 · (760) 727-3711 · FAX (760) 727-4427
<http://www.appliedmembranes.com> · sales@appliedmembranes.com